

Class A Customs
1130 County Road 6
Elkhart, IN 46514
PH: 574-206-0101
cs@classacustoms.com



June 22, 2023

Class A Customs was required to remove the NSF logo from all water tanks in June 2020, the tanks continue to be made from the same [NSF Certified Materials](#), built in the same way, built on the same machines, and built in the same building here at Class A Customs.

The NSF Company does not allow for end users of NSF Certified Materials to use the NSF logo unless *each kind of item* that is produced has a certification paid for each year. This would mean every style of tank we make, even though they are made using the same NSF Certified Materials, made in the same process, made on the same machine, we would need to pay to use the logo on each item every year.

All of Class A Customs Fresh/Gray water tanks are manufactured using [DOW NSF International NSF/ANSI Std 61 approved Medium Density Polyethylene \(MDPE\) Resin](#)

Because Class A Customs was verified to used and continues to use NSF Certified Materials to build our tanks we are allow to link directly to the NSF website materials page and are allowed to state the tanks are made from NSF Certified Materials.

The NSF associate Class A Customs was contacted by and worked with was;
Antonio Acree
Quality Representative, Quality & Compliance
aacree@nsf.org

NSF International | nsf.org
789 N. Dixboro Road, Ann Arbor, MI, 48105, U.S.A
1-800-NSF-MARK

Your inspector can validate this information with NSF by contacting them directly.

*Before you build or modify a unit **verify rules and regulations**, codes vary by *local* health departments, not state. We are not aware what tanks or items you will need.*

If you have more questions on this please feel free to contact us.

Customer Service,
Class A Customs

www.classacustoms.com

Part #	Gallons	Length +/- .25"	Width +/- .25"	Height +/- .25"	Installed Fittings	
<u>T-0500</u>	5	17.5	7	9.5	One) 1.5" Female NPT - closed	Three) .5" Female NPT - open
<u>T-0700</u>	7	23.75	7	9.75	One) 1.5" Female NPT - closed	Three) .5" Female NPT - open
<u>T-1000</u>	10	19	9	14	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-1300</u>	13	21	9	16	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-1500</u>	15	25.5	11.15	11.75	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-1600</u>	16	26	9	16	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-1800</u>	18	23	10.5	17.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-2000</u>	20	32.5	11.75	11.75	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-2100</u>	21	34	9	16	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-2300</u>	23	39.5	8.75	14.75	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-2500</u>	25	33.5	10	17	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-2872</u>	28	56.5	11	17	NO Fittings Installed	NO Fittings Installed
<u>T-2955</u>	29	74	9	17.5	NO Fittings Installed	NO Fittings Installed
<u>T-3000</u>	30	34.5	12	17.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-3300</u>	33	36	12	17.75	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-3500</u>	35	38.5	12	17.25	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-3687</u>	36	42	13	20	One) 1.5" Female NPT - closed	Three) .5" Female NPT - open
<u>T-4000</u>	40	39.5	13	18	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4100</u>	41	39	16.625	16	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4159</u>	41	71	10	14.625	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4200</u>	42	27.5	15.25	22.5	Three) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4320</u>	43	25.5	17.75	23	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4600</u>	46	42	14	18	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-4812</u>	48	58.5	11.25	17.75	NO Fittings Installed	NO Fittings Installed
<u>T-5000</u>	50	38.25	14.25	22.25	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-5500</u>	55	37.5	17.5	19.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-6500</u>	65	44.5	17.5	19.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-6632</u>	66	33.375	25.375	18.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-7500</u>	75	50.5	17.5	19.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-10000</u>	100	50	18	26	Six) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>T-12500</u>	125	64.5	18	26.5	Six) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>UM-1000</u>	10	24	8.5	13	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>UM-1500</u>	15	36	8.5	13	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>UM-2000</u>	20	48	8.5	13	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>UM-2500</u>	25	38	8.5	20.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open
<u>UM-3000</u>	30	48	8.5	20.5	Two) 1.5" Female NPT - closed	Two) .5" Female NPT - open